

JEVALux[®] FLL-25K

Flange-mounted LED vacuum chamber illumination

- easy-to-clean light conductor on flange DN25KF
- powerful LED as light source outside the vacuum chamber
- light coupling via glass cylinder in four different lengths
- perfect illumination by light scattering at the end of cylinder
- quickly mountable
- no heating by light source inside the vacuum chamber
- low power input
- power supply voltage +12 – +24 VDC
- optionally with plug-in power supply and switch for two brightness levels or 5 m cable with angled connector alternatively



Versions


JEVALux® FLL-25K-xxx-PS LED vacuum chamber illumination on stainless steel flange DN25KF
installation depth (xxx) 50, 75, 100 or 125 mm (measured from the sealing face of the flange)
switch for two brightness levels
plug-in power supply 24 VDC with connecting cable 1.80 m and straight connector at flange

JEVALux® FLL-25K-xxx-L LED vacuum chamber illumination on stainless steel flange DN25KF
installation depth (xxx) 50, 75, 100 or 125 mm (measured from the sealing face of the flange)
connecting cable 5 m and angled connector at flange

Technical Data

Light source:	Model:	LED
	Luminous flux:	550 lm max.
	Color temperature:	6000 K
Vacuum connection:	Flange:	KF standard DN25KF
	Mounting position:	arbitrary
	Installation depth:	50, 75, 100 or 125 mm (measured from the sealing face of the flange)
Material:	Medium-contacting materials:	Stainless steel 1.4301 AR-GLAS® BondLock® 0185, extremely low gas emission
Mains connection:	Voltage:	+12 – +24 VDC
	Power consumption:	5 W max.
	Connection:	power socket for plug-in power supply
Environment:	Pressure range:	1·10 ⁻⁹ – 1500 mbar
	Temperature:	Storage: -20 – +60 °C Operation: +5 – +45 °C (sea level)
	Degassing temperature:	80 °C max. at flange
	Relative humidity:	80 % max. to 30 °C) decreasing to 50 % max. (over 40 °C)
	Usage:	indoors (altitude 2000 m above sea level)
Weight:	Protection class:	IP40 (in mounted condition)
		0,25 kg approx.

Dimensions



(Dimensions in mm)

More information under:

JEVATEC GmbH
D-07743 Jena, Schreckenbachweg 8
Phone: +49 3641 3596-0
Fax: +49 3641 3596-39
E-mail: info@jevatec.de

JEVATEC
Ideen in der Vakuumtechnik
www.jevatec.de

